

9. BS-6020RF/TRF Laboratory Metallurgical Microscope



BS-6020TRF

Introduction

BS-6020RF/TRF metallurgical microscopes are high level professional microscopes which are specially designed for metallurgical analysis. With excellent optical system, ingenious stand and convenient operation, they will be your best choice.

Feature

1. Laboratory metallurgical microscope, including bright field, dark field and polarization observation system.
2. Powerful transmitted and reflected system with Kohler illumination.
3. Ideal instrument for metallurgical analysis, industry inspection and science research.

Application

BS-6020RF/TRF are widely used in institutes and laboratories to observe and identify the structure of various metal and alloy, they also can be widely used in electronics, chemical and instrumentation industry, observe the opaque material and transparent material, such as metal, ceramics, integrated circuits, electronic chips, printed circuit boards, LCD panels, film, powder, toner, wire, fibers, plated coatings, and other non-metallic materials and so on.

Specification

Item	Specification	BS-6020RF	BS-6020TRF
Optical System	Infinite optical system	●	●
Viewing Head	Siedentopf trinocular viewing head, inclined at 30°, interpupillary distance 48mm-75mm	●	●
Eyepiece	Extral wide field eyepiece EW10×/22mm, eyepiece tube Ø30mm	●	●
Infinite Plan Achromatic Objective	5×/ 0.12/∞/ - (BF) WD 15.5mm	●	●
	10×/ 0.25/∞/ - (BF&DF) WD 10.0mm	●	●
	20×/ 0.4/∞/ 0 (BF&DF) WD 4.3mm	●	●
	50×/ 0.75/∞/ 0 (BF) WD 0.32mm	●	●
	100×/ 0.8/∞/ 0 (BF) WD 2mm	●	●
	40×/ 0.65/∞/ 0.17 WD 0.54mm		●
	100×/ 1.25/∞/ 0.17 WD 0.13mm		●
	5×/ 0.12/∞/ - (BF&DF) WD 12mm	○	○
	40×/ 0.6/∞/ 0 (BF&DF) WD 2.9mm	○	○
	50×/ 0.75/∞/ 0 (BF&DF) WD 0.32mm	○	○
100×/ 0.8/∞/ 0 (BF&DF) WD 2mm	○	○	
Maximum Sample Height	30mm		●
	50mm	●	
Reflected Light	24V/100W Halogen light, Brightness adjustable	●	●
	Kohler illumination and aspherical condenser	●	●
	Polarizer and analyzer	○	○
	An integrate device for polarizer and analyzer	○	○
	Blue, Green, Yellow and Ground glass filter	●	●
Transmitted Light	Swing-out condenser NA0.9/ 0.25		●
	24V/100W Halogen light and aspherical condenser		●
	Blue filter		●
Filter	ND25, ND6	○	○
Focusing	Coaxial Coarse and Fine Adjustment, Fine Division 0.001mm, Coarse Stroke 37.7mm per Rotation, Fine Stroke 0.1mm per Rotation, Moving Range 30mm	●	●
Nosepiece	Backward quintuple nosepiece	●	●
Stage	Double layer mechanical stage(without hole) 186×138mm/ 74mm×50mm	●	
	Double layer mechanical stage 186×138mm/ 74mm×50mm		●
	Glass specimen preparation plate	○	○
	Specimen preparation plate		●
	Slide glass		●
Accessories	Specimen Presser	○	○
	Photo Attachment	○	○
	Video Attachment, C-mount 1×, 0.5×	○	○

Note: ●Standard Outfit, ○Optional

Accessory



Specimen Presser

Sample Image

